# **Machine** VISION DIRECT

## SP645 NEAR-IR/MID-RED DICHROIC BLOCK SHORTPASS FILTER

#### MidOpt Shortpass (IR-Cut) Filters

- Designed to have a sharp transition between shorter wavelengths (which are passed) and longer wavelengths (which are blocked)
- Peak transmission ≥90%\*
- Can be used with Longpass Filters for a custom, finetuned Bandpass Filter
- Anti-reflection coated for maximum transmission
- Exceptional surface quality; 40/20 scratch/dig
- Available in wavelength ranges from 340nm to 785nm

#### Shortpass Filter Information



Often thought of as "IR-cut" filters, Shortpass Filters are specifically designed to pass a broad spectrum of shorter wavelength light, while blocking longer visible (VIS) and near-infrared (NIR) wavelengths.


#### SP Series - VIS Pass/NIR Block Filters

- Commonly placed over the camera's image sensor to block NIR light and achieve natural color rendition
- Used as a hot mirror to reduce unwanted heat build-up caused by IR radiation

**APPLICATIONS**: Shortpass Filters are commonly used in color imaging to achieve natural color rendering. They can also be used to protect the sensor from NIR laser damage or to reduce IR radiation or "camera bloom" created during hot metal or glass extrusion processes.








Useful Range:	400-640nm	
Cut-off Wavelength 50% T:	645nm	
Tolerance:	+/- 10nm	
Peak Transmission:	≥90%	
Surface Quality:	40/20	

2

Our most popular near-IR blocking filter for inside-the-camera applications. Also referred to as an infrared cut filter, these filters limit the amount of infrared radiation that reaches delicate CCD and CMOS sensors. Near-IR blocking is unusually exceptional in the case of these filters. CCD/CMOS imagers are very sensitive to infrared radiation and, often, deep



red wavelengths as well. Using a SP645 filter will reduce or prevent a reddish, washed out color of the final image. These filters are 1mm thick.





## SP645 TRANSMISSION DATA (TYPICAL)

Wavelength (nm)	Transmission (%)	Wavelength (nm)	Transmission (%)	Wavelength (nm)	Transmission (%)
1100	73.35	790	0.01	480	90.66
1090	50.29	780	0.01	470	89.95
1080	21.95	770	0.01	460	88.58
1070	7.04	760	0.01	450	87.82
1060	2.87	750	0.02	440	86.80
1050	1.87	740	0.01	430	85.98
1040	1.59	730	0.01	420	84.45
1030	1.22	720	0.01	410	82.83
1020	0.63	710	0.04	400	79.51
1010	0.23	700	0.06	390	73.27
1000	0.08	690	0.07	380	60.71
990	0.04	680	0.23	370	19.42
980	0.03	670	1.62	360	0.08
970	0.04	660	5.94	350	0.00
960	0.06	650	47.88	340	0.00
950	0.05	640	89.35	330	0.00
940	0.03	630	90.08	320	0.00
930	0.01	620	92.71	310	0.00
920	0.01	610	93.03	300	0.00
910	0.02	600	92.70	290	0.00
900	0.03	590	92.13	280	0.00
890	0.02	580	92.58	270	0.00
880	0.02	570	91.67	260	0.00
870	0.00	560	91.04	250	0.00
860	0.00	550	92.18		
850	0.00	540	91.83		
840	0.00	530	91.22		
830	0.00	520	92.20		
820	0.00	510	90.79		
810	0.00	500	91.75		
800	0.01	490	90.92		




# **Machine** VISION DIRECT


## STANDARD THREADED MOUNT DIMENSIONS

#### NOTES:

- 1. Inner and outer threads are of the same size and pitch.
- 2. Filter mount and retaining ring are black anodized aluminum.
- 3. All dimensions indicated in mm.
- 4. Tolerance: +/-0.3mm.

Mount Size	А	В	С	D
M13.25 x P0.5	14 <mark>.3</mark>	10.6	<b>7.5</b>	5.7
M22.5 x P0.5	2 <mark>4</mark>	18.5	7	5.2
M25.5 x P0.5	27 <mark>.5</mark>	21	7	5.2
M27 x P0.5	29	22.5	7	5.2
M30.5 x P0.5	32.5	25.5	7	5.2
M34 x P0.5	36	29	7	5.2
M35.5 x P0.5	37.5	<mark>3</mark> 0.5	7	5.2
M37 x P0.75	39	<mark>31</mark> .9	6.5	4.5
M37.5 x P0.5	39.5	<mark>32.</mark> 5	7.2	5.2
M39 x P0.5	41	<mark>3</mark> 4	7	5.2
M40.5 x P0.5	42.5	35.5	7	5.2
M43 x P0.75	45	38	7	5.2
M46 x P0.75	48	41	7	5.2
M48 x P0.75	50	43	7	5.1
M49 x P0.75	5 <mark>1</mark>	44	7	5.2
M52 x P0.75	5 <mark>4</mark>	47	7	5.2
M55 x P0.75	57	50	7	5.2
M58 x P0.75	60	52.9	6.5	4.5
M62 x P0.75	64	57.1	7	5.2
M67 x P0.75	70	61.8	6.5	4.5
M72 x P0.75	75	66.9	6.5	4.5
M77 x P0.75	80	71.9	6.5	4.5
M82 x P0.75	85	76.8	6.5	4.5
M86 x P1.0	89	80.8	6.5	4.5
M95 x P1.0	98.2	89.9	10	7.1
M105 x P1.0	109.8	100	11	8








© Midwest Optical Systems – Rev 1/2016




## C-MOUNT DIMENSIONS (-25.4)

C-Mount is available on filters with a substrate thickness of 1mm or less



### C-MOUNT SIS DIMENSIONS (-25.4-SIS)

C-Mount SIS is available on filters with a substrate thickness greater than 1mm and less than or equal to 3.5mm





# **Machine** VISION DIRECT

### MOUNTS FOR ANY SYSTEM

#### **Mount Sizes**

> THREADED



Midwest Optical Systems is the world's leading resource in machine vision filters and optical solutions. MidOpt's innovative filter designs ensure flawless control, dependable results and unmatched image quality. Mounting solutions are available for any system for lenses with and without filter threads, the exclusively designed 25.4<sup>™</sup> C-Mount, and custom fabrication of unmounted shapes and sizes.



<ul> <li>&gt; THREADED MOUNT Designed for Lenses with Filter Threads</li> <li>MidOpt offers the largest variety of filters in-stock and ready to ship</li> <li>Sizes available: M13.25-M105</li> <li>Black anodized aluminum</li> <li>Custom thread sizes are available upon request</li> </ul>
CREATE PART #: Select a filter and add a mount size (e.g. M27) Example: BP470-27
<ul> <li>&gt; 25.4<sup>™</sup> C-MOUNT Threads into all C-Mount Cameras</li> <li>25.4<sup>™</sup> C-Mount Camera Filter exclusively designed by MidOpt to thread directly into any C-Mount Camera between the lens and sensor</li> <li>Recommended for use with wide angle lenses to prevent vignetting and angle shift</li> <li>Helpful in applications with space constraints and lenses without filter threads</li> <li>Custom installation wrench included</li> </ul>
CREATE PART #: Select a filter and add "-25.4" Example: BP470-25.4
<ul> <li>SLIP MOUNT Designed for Wide Angle Lenses Without Filter Threads</li> <li>Accommodates standard threaded mounts</li> <li>Low profile and oversize diameter design prevents wide angle lens vignetting</li> <li>Includes black Delrin<sup>®</sup> Slip Mount adapter plus Threaded Mount Filter</li> </ul>
CREATE PART #: Select a filter, use "S" for slip and add the outside diameter of lens in mm (e.g. 43mm) Example: BP470-S43
<ul> <li>UNMOUNTED</li> <li>Any MidOpt filter type can be provided as an Unmounted Filter</li> <li>Custom shapes and sizes are typically available within a two week lead time with many shipped same day</li> </ul>

#### CREATE PART #

CIRCLE: Use "D" and add diameter in mm (e.g. 19mm) Example: BP470-D19 SQUARE: Use "R" and add side measurement in mm (e.g. 15mm) Example: BP470-R15 RECTANGLE: Use "R" and add length in mm (e.g. 30mm) x width in mm (e.g. 15mm) Example: BP470-R30x15




#### > CUSTOM SOLUTIONS FOR M12 MOUNT LENSES

- Offered in aluminum slip mount over the lens
- Can be optically cemented behind the lens

## HOW TO ORDER

To order a filter with a threaded mount, first select a filter (e.g. BP470) and add the mount size (e.g. M27) to build your part number (e.g. BP470-27).





#### C-MOUNT M25.4™

1.0

M95

M105 1.0

SLIP MOUNT

Threadea Mount
M22.5
M30.5
M40.5
M46
M55
M62
M72
M82
M105

#### UNMOUNTED

Custom Shapes & Sizes Available

#### M12 MOUNT

Outside Diameter Range 13.2-14.2 S14A 14.3-15.0 S15A



7


# **Machine** VISION DIRECT

### **MIDOPT STABLEDGE®**

#### Minimize the Effects of Short Shifting

MidOpt StablEDGE<sup>®</sup> optical filters are specifically designed to be less susceptible to effects from angular shifting seen when optical filters are placed in front of short focal length (<12mm) camera lenses. This feature is becoming increasingly important as today's trend in machine vision imaging progresses towards more compact inspection layouts, which utilize less space – forcing the camera and lens closer to the subject. As a result, short focal length lenses are now more widely used than ever before.

Using a traditional coated interference filter in these more compressed configurations results in contrast loss toward the edges of the image. Because of the angle imposed by the field of view (FOV) of the lens, the passband shifts and allows short wavelength ambient light to overwhelm the subject. Light from LED or laser diode lighting is also cut off. In contrast, peak transmission of MidOpt's StablEDGE® filters is not significantly altered, and effects due to short shifting are minimized.



StablEDGE® filters take advantage of absorptive filter glass to form the leading edge of the filter passband. This assures no shifting in this region, even when the lens FOV exceeds 100°. Filter glasses also offer far superior lower wavelength blocking of ambient light, sharp transition slopes and unmatched durability. MidOpt's StablEDGE® Filter cut-off slopes utilize interference filter coatings, however the cut-off slope is positioned to be sufficiently broad, and the Gaussian passband profile ensures that excessive ambient light is not allowed to degrade image contrast. Thus, shifting will not significantly encroach into peak transmission, assuring angular insensitivity over the desired range.

Among all machine vision filter manufacturers, MidOpt is unique in incorporating StablEDGE® technology across a full range of products. StablEDGE® designs are less angle-of-incidence sensitive, inherently more rugged, and are environmentally stable.

