

SP-5000M-CXP4

Technical Datasheet

See the possibilities

Lince5M



Apex Series



Spark Series area scan cameras are the perfect choice for machine vision applications demanding high quality images with the highest possible throughput. They feature the latest CMOS imagers delivering high resolution images at speeds as much as 10 times faster than traditional CCD cameras.

For example, 45-megapixel (MP) models can deliver over 50 fps output while some 5-MP models run at 250 fps or more. Using the region-of-interest (ROI) feature, even higher frame rates can be achieved.

Specification Highlights

SHUTTER:

SENSOR: Lince5M

FRAME RATE: 253 fps

PIXEL SIZE: $5.0 \times 5.0 \mu m$ **INTERFACE:** CoaXPress-4-Cable (PoCXP)

Global Shutter

5 MP LENS MOUNT: C-Mount **RESOLUTION MP:**

SPECTRUM: Monochrome (Visible + NIR) RESOLUTION WxH: 2560 x 2048 px

FORMAT:






_					
ı	Specificatio	ns	SP-5000-CXP4		
	Sensor		1" CMOS global shutter		
	System clock		72 MHz (for pulse generator)		
	Frame rate, full frame		253 frames/sec. @ 8/10/12-bit, CXP6_X4		
	Active area Cell size Active pixels		12.8 mm (h) x 10.2 mm (v), 16.39 mm diagonal		
			5.0 μm (h) x 5.0 μm (v)		
			2560 (h) x 2048 (v)		
	Read-out modes				
	Full ROI		2560 (h) x 2048 (v) up to 253 fps Any start line, any height in 2 line steps, with X offset and width in 64 pixel steps		
	Binning		1x2, 2x1, 2x2 (monochrome only)		
	Color interpolation (SP-5000C)		24-bit RGB output at up to 53 fps		
100	EMVA 1288 Paramet Absolute sensitivity (Absolute sensitivity Maximum SNR (mo Maximum SNR (cold	mono) (color) no)	10-bit output format 23.50 p (λ = 525 nm) 36.08 p (λ = 525 nm) 41.48 dB 38.00 dB		
	Traditional SNR*	mono	>55 dB (0 dB gain)		
	Vidoo signal	color	>53 dB (0 dB gain, green)		
	Video signal output	mono color	8/10/12-bit monochrome 8/10/12-bit Bayer or 24-bit RGB		
	Interface		CoaXPress v1.0 (CXP-6, DIN 1.0/2.3 connectors) Link Configs: CXP6_X4, CXP6_X2, CXP6_X1, CXP3_X4, CXP3_X2, CXP3_X1		
l	Gain		Manual/automatic 0 dB to +24 dB		
	White balance (SP-5000C)		Manual, one-push auto, or continuous (3000к to 9000к)		
	Gamma		0.45-1.0 (16 steps) or 256-point LUT		
	Synchronization		Internal		
	Trigger input		TTL, CXP, Pulse Generators (4), Software, NAND Out (2), GPIO		
	Trigger modes		EPS, PIV, Trigger Width, Timed RCT (with ALC), Sequence		
	Electronic shutter Timed exposure Auto shutter		10 µs to 8 sec in 1 µs steps 1/250 to 1/100000 sec.		
	Auto Level Control (ALC)		Shutter range from 1/253 to 1/100000, gain range from 0 dB to +24 dB, auto iris control Tracking speeds and max values adjustable.		
	Pre-processing functions		Flat field correction, color shading correction (SP-5000C), blemish compensation (512 pixels)		
	3-axis control		Programmable control of motorized lenses, pan/tilt heads, and other analog accessories		
	Operating temperature		-45°C to +70°C [†]		
	Storage temperature		-45°C to +70°C		
	Humidity		20 - 80% non-condensing		
	Vibration		10 G (20Hz to 200Hz XYZ)		
	Shock		80 G		
	Regulations		CE (EN61000-6-2, EN61000-6-3), FCC Part 15 class B, RoHS/WEEE		
	Power	12-pin PoCXP	12V to 24V DC ± 10%. 7.8W typical @ 12V 24V DC ± 2V. 7.8W typical @ 24V		
	Lens mount		C-mount		
Ì	Dimensions (H x W	x L)	62 mm x 62 mm x 55.5 mm		
ľ	Weight		215 g		
	Ordering Information				
	SP-5000M-CXP4		Monochrome camera with four-channel CoaXPress		

Dimer	nsions
SS SS GE MAD Depoth S C Mount	5.2.0,3 50 9.8.24.5
	9. 0 24. 5

		_			
	DC In / Trigger		Auxiliary Connector		
				10	
HIR	OSE HR10A-10R-12PB-	01	Type: 3260-1053(55) HIROSE		
`onn	ector Pin-out		or equivalent		
Pin	Signal	Pin	Name	Note	
1	GND	1	Drive Iris+		
2	+12V to +24V DC input	2	Drive Focus+	Motorized Lens	
3	GND	3	Drive Zoom+	Motorized Leris	
-	NC	4	Common		
4		5	GND	GND	
5	Opto In-	5	OND	OND	
	Opto In-	6	P-Iris Out A+	OND	
5	•	6 7	P-Iris Out A+ P-Iris Out A-	P-Iris Lens	
5	Opto In+	6 7 8	P-Iris Out A+ P-Iris Out A- P-Iris Out B+		
5 6 7	Opto In+ Opto Out-	6 7 8 9	P-Iris Out A+ P-Iris Out A- P-Iris Out B+ P-Iris Out B-	P-Iris Lens	
5 6 7 8	Opto In+ Opto Out- Opto Out+	6 7 8	P-Iris Out A+ P-Iris Out A- P-Iris Out B+		
5 6 7 8	Opto In+ Opto Out- Opto Out+ TTL out 1	6 7 8 9	P-Iris Out A+ P-Iris Out A- P-Iris Out B+ P-Iris Out B-	P-Iris Lens	



*Traditional SNR is based on random noise in a single frame, where EMVA SNR measurements consider more comprehensive noise sources and variance over time. For a more complete description, see the manual.

 $^\dagger \text{Reduced performance may occur when operating outside the standard range of -5°C to +45°C$

SP-5000C-CXP4



Color camera with four-channel CoaXPress



Product Highlights

- Large format 5 MP CMOS imager (global shutter)
- Up to 253 fps at full resolution
- 5.0 µm square pixels in a 5:4 aspect ratio
- 60 dB linear dynamic range with up to 84 dB piece-wise HDR modes
- Analog and digital gain control for less quantized noise in low-light situations
- Exposure control from 10 µs (1/100,000) to 8 seconds in 1 µs steps
- 2X binning for increased sensitivity (monochrome only)
- ROI modes for flexible readout, windowing, or increasing frame rate
- Monochrome or color models with built-in color interpolation on color model
- 8/10/12-bit digital output over four-channel CoaXPress interface
- Accepts power via CoaXPress or separate 12-pin connector
- C-mount lens mount
- Automatic Level Control (ALC) for dynamic lighting conditions
- Programmable P-iris lens control or 3-axis control for operation of motorized lenses, pan/tilt heads, or other analog accessories

Additional Product Images



Company and product names mentioned in this datasheet are trademarks or registered trademarks of their respective owners. JAI A-S and Machine Vision Direct, LLC Cannot be held responsible for any technical or typographical errors and reserves the right to make changes to products and documentation without prior notice

