

LLPX-H Light Panel

PRODUCT DATA SHEET



- ✓ PNP and NPN trigger signal input
- ✓ 30 mm industrial extrusion
- ✓ 5-pin M12 quick connect
- ✓ Custom light sizes available
- ✓ Custom hole placement and sizing available

Rev. 2021/07/08

smartvisionlights.com

PRODUCT DESCRIPTION

In the LLPX-H Light Panel Series, an optically clear internal light dispersion grid and a matte-white-finished backing plate allow more light to be reflected up and out through the diffusion acrylic. The LLPX-H features Multi-Drive[™], which allows the user to operate the light in constant ON operation or OverDrive[™], depending on wiring method. The industry-standard 5-pin M12 connector makes for simple wiring. The 1–10VDC analog signal line gives the user total control over intensity in continuous operation. Removing the signal puts the light into OverDrive[™] strobe mode. Custom placement, sizing, and number of holes available upon request.

PRODUCT SPECIFICATIONS

	CONTINUOUS OPE	RATION	OVE			
Electrical Input	24VDC +/-5%					
PNP Line	2.8 mA @ 4VDC 8.8 mA @ 12VDC 17.6 mA @ 24VDC					
NPN Line	14.4 mA @ Common (0VDC)					
OverDrive™ Strobe Mode	Not applicable		Connect pin 5 to GND			
overblive strobe mode				figuration for more information)		
Strobe Duration	Not applicable		Min. 10 µs			
			(see SafeStrobe [™] Technology for more information)			
Duty Cycle	Not applicable		Max. 10%			
Strobe Input	Not applicable		PNP: +4VDC or greater to activate			
			NPN: GND (<1VDC) to activate			
Continuous Operation Mode	NPN can be tied to ground OR PNP can be tied to 24VDC (not both)		Not applicable			
continuous operation mode						
On/Off Input	PNP: +4VDC or greater to activate NPN: GND (<1VDC) to activate		Not applicable			
Connection	5-pin M12 connector					
Ambient Temperature	-18°-40° C (0°-104° F)					
IP Rating	IP50					
Compliances	CE, RoHS, IEC 62471					
Warranty	10 year warranty.					
	For complete warranty information, visit smartvisionlights.com/warranty.					
Standard Light Sizes	Input Current	Wat	tage	Weight		
2			<u> </u>			
<u>306 mm x 306 mm</u>	1.26 A		24 W	~3.08 kg		
459 mm x 459 mm	1.98 A	47.5	52 W	~5.74 kg		

CUSTOMIZE

Smart Vision Lights can customize an LLPX-H to meet your needs.

Size

SVL can customize an LLPX-H to the size you need — up to 4800 x 1180 mm. When requesting a custom LLPX-H, include the following: size (length x width) in millimeters, what side the 5-pin M12 connector should be placed on, and desired wavelength (color).

Holes

Holes can be placed in just about any location on the LLPX-H. When requesting custom hole placement, include number of holes needed, size of holes in millimeters and desired locations.




RESOURCE CORNER

Additional resources, including CAD files, videos, and application examples, are available on our website.

(2)

WIRING CONFIGURATION

CONTINUOUS OPERATION MODE



Pin layout for light (male connector)

Pin Function Signal Wire Color For the light to function properly, apply either a PNP or NPN 1 Power In +24VDC BROWN signal, not both 2 NPN **Sinking Signal** WHITE Failure to supply light with correct input current will result in GND BLUE 3 Ground non-repeatable lighting. (see Product Specifications for requirements) 4 PNP BLACK Sourcing Signal 1-10VDC 5 Intensity Control

*Some cables use green/yellow for pin 5.

For maximum intensity tie pin 5 to pin 1 at +24 VDC.

For maximum intensity tie pin 5 to pin 1 at +24 VDC.

For continuous mode, PNP (pin 4) can be tied to +24 VDC (pin 1) or NPN (pin 2) can be tied to ground (pin 3).

OVERDRIVE[™] OPERATION MODE

3 Blue	Pin	Function	Signal	Wire Color	
	1	Power In	+24VDC	BROWN	Failure to supply light with correct input current will result in
	2	NPN	Sinking Signal	WHITE	non-repeatable lighting.
	3	GND	Ground	BLUE	(see Product Specifications for requirements)
O O	4	PNP	Sourcing Signal	BLACK	
	5	OverDrive [™] Signal	Ground	GREY*	
1 Brown	*Soi	me cables use green/yellow fo	or pin 5.		

1 Brown +24 VDC Pin layout for light (male connector)


Grey

Black

DUTY CYCLE (OVERDRIVE[™] MODE ONLY)

This section applies only to OverDrive[™] strobe mode.

The duty cycle (D) is related to the strobe time (ST) and rest time (RT).



Light follows strobe pulse - the light output will track the width of the strobe pulse

Maximum duty cycle for OverDrive[™] light is 10% (0.1) Note: Strobe time is limited by the strobe rate.

MULTI DRIVE

Multi-Drive[™] offers the best of both worlds. Continuous operation and OverDrive[™] mode (high-output strobe/pulse) are available in a



RT = Rest Time

ST = Strobe Time

D = Duty Cycle

Example

 $90 \text{ ms} = \frac{10 \text{ ms}}{.1} - 10 \text{ ms}$

Rest Time is 90 ms for 10 ms Strobe Time

single light. Other advantages of Multi-Drive™ include faster imaging and capture/freeze motion on high-speed lines.

The Multi-Drive[™] feature allows the user to run the light continuously or in OverDrive[™] at the maximum allowed intensity by simply setting the product configuration. OverDrive[™] operation has **up to eight times** the power of continuous operation.

Calculating Rest TimeCalculating Strobe Rate $RT = \frac{ST}{-} - ST$ $SR = \frac{D}{-}$

$$SR = \frac{D}{ST}$$

SR = Strobe Rate (strobes per second) ST = Strobe Time (seconds) D = Duty Cycle

Example $1000 = \frac{0.1}{0.0001}$ Strobe Rate is 1000 strobes per second

Calculating Duty Cycle

 $D = ST \times SR$

SR = Strobe Rate (strobes per second) ST = Strobe Time (seconds) D = Duty Cycle

Example

 $0.1 = 0.0001 \times 1000$

Duty Cycle is 10% (0.1)

```
EDGE LIT
```

The LLPX-H is edge lit, which means the light comes from each of the four edges. This produces a very homogeneous light output.



LLPX-459x459 shown

(LED size and spacing not shown to scale)

3

SAFESTROBE[™] TECHNOLOGY

SafeStrobe[™] technology applies safe working parameters to ensure that high-current LEDs are not damaged by being driven beyond their limits, such as maximum strobe time or duty cycle. This is especially beneficial for overdriving our high-current LEDs.


PRODUCT DRAWING

CAD files available on our website. Dimensions are in mm.

306 mm x 306 mm

. lyp. Ø9 THRU ALL ∟ Ø17.30∓24 306 active area





EYE SAFETY

According to IEC 6247: 2006. Full documentation available upon request.

Notice

Exempt Group: No photobiological hazard to eyes or skin even for continuous, unrestricted use. Applicable for wavelengths 625, 850, 940, 1050, 1200, 1300, 1450, and 1550.

Caution

Risk Group 1: Possibly hazardous optical radiation emitted from this product. Do not stare at operating lamp. May be harmful to eyes. Safe for most applications except for prolonged exposure. Applicable for wavelengths 470, 505, 530, and WHI.

LLPX-H Series of Backlights works best for:






Radial




🛜 smart vision lights





🛜 smart vision lights




SIZING A LIGHT

When sizing a light for the most consistent/homogeneous illumination, best practice is to follow the W Rule. The W Rule states: The working distance (WD) is equal to the size of the part (X) and the size of the light is twice the size of the part.

THE W RULE:

The working distance is equal to the size of the part. The size of the light is twice the size of the part.

If the working distances needs to be increases, the light also needs to increase in size to remain homogeneous. 2X




(5)

OPTICAL PERFORMANCE

The LLPX-H offers a very diffuse light pattern.

OPTICAL PERFORMANCE FOR THE LLPX-H

Rating	Illuminance (Lux)			
Average Intensity Rating	42,000			
Illuminance measurement taken at surface of LLPX-H				



MOUNTING

Smart Vision Lights recommends using **drop-in T-nuts** for mounting an LLPX-H backlight.

Hardware included with light:

(2) M5 x 10 mm screws (hex)

(2) Drop-in T-nuts

NOTE

Removing corner cubes of light may result in voiding of warranty.




PATTERN AREA LIGHTING

Pattern Area Lighting (PAL) is used for isolating defects on uneven, highly specular, and/or clear surfaces, which can be difficult with standard lighting methods. PAL allows for isolating a defect in a single image acquisition. With PAL, small defects will reflect off the surface at an equal but opposite angle. Distortion of the reflected image can also reveal surface deformations.

How to use PAL

- For backlighting a transparent object, the light is positioned beneath the object.
- For front lighting, position the light where the light pattern will be directed on the surface at an angle.
- A camera is positioned to capture the reflection of the light source.
- The camera lens is adjusted to focus on the surface defect.
- The camera should also image the light source pattern, but the pattern does not need to be in tight focus.
- The depth of field for the lens should be adjusted to include both the light source pattern and the defect in one im-



Customized line and circle sizes available upon request.

NOTE

Smart Vision Lights can customize just about any pattern needed to meet application requirements.

6

ACCESSORIES



GLOSSARY

This glossary covers all Smart Vision Lights product families; some content in this section may not apply to this specific light.

TERMINOLOGY

OverDrive[™] Lights include an integrated high-pulse driver for complete LED light control.

Continuous Operation Lights stay on continuously.

Multi-Drive[™] Combines continuous operation and OverDrive[™] strobe (high-pulse operation) mode into one easy-to-use light. Built-In Driver The built-in driver allows full function without the need of an external controller.

Camera to Light Connecting the light directly to the camera, without the need for additional controllers or equipment.

Polarizers Filters that reduce reflections on specular surfaces.

Diffuser Used to widen the angle of light emission, reduce reflections, and increase uniformity.

TYPES OF ILLUMINATION









Line





Bright Field



Direct

Diffuse Panel





Backlight

Radial

(7)

COMMON COLOR/WAVELENGTHS LEGEND

Wavelength options range from 365 nm to 1550 nm. Additional wavelengths available for many light families.



See Part Number section for this light's available standard wavelengths.



Shortwave infrared LEDs are available in 1050 nm, 1200 nm, 1300 nm, 1450 nm, and 1550 nm. Check Part Number section to see if *this light* is available in SWIR wavelengths.